


NG Series Nylon Hose

Ordering Information and Dimensions

Custom Hose Assemblies—Twin and Vent Hoses

Build a hose assembly ordering number by combining the designators in the sequence shown below.



Typical Ordering Number

1 **2** **3** **4** **5** **6** **7** **8** **9** **10** **11**
 SS - NGV 6 - S6 T6 S4 P6 - 24 - 1 3 - X

1 Material

End Connections

SS = 316 stainless steel

2 Hose

NGT = NG series twin nylon hose (Ω)

NGV = NG series vent nylon hose (Ω)

3 Nominal Fill Hose Size, in.

4 = 1/4

6 = 3/8

4 Fill Hose Nozzle End Connection

5 Fill Hose Dispenser End Connection

6 Vent Hose Nozzle End Connection

7 Vent Hose Dispenser End Connection

See **End Connection Designator** column in tables on page 323.

For fitting dimensions, see **End Connection** tables, page 323.

8 Overall Length (Fill and Vent)

Insert length in inches.

9 Vent Hose Nozzle End Length Adjustment

Positive

X = None

1 = 2 in.

2 = 4 in.

3 = 6 in.

4 = 8 in.

5 = 10 in.

6 = 12 in.

7 = 15 in.

8 = 18 in.

9 = 21 in.

0 = 24 in.

Negative

X = None

A = 2 in.

B = 4 in.

C = 6 in.

D = 8 in.

E = 10 in.

F = 12 in.

G = 15 in.

H = 18 in.

J = 21 in.

K = 24 in.

Illustration shows adjustment 1.

10 Vent Hose Dispenser End Length Adjustment

Positive

X = None

1 = 2 in.

2 = 4 in.

3 = 6 in.

4 = 8 in.

5 = 10 in.

6 = 12 in.

7 = 15 in.

8 = 18 in.

9 = 21 in.

0 = 24 in.

Negative

X = None

A = 2 in.

B = 4 in.

C = 6 in.

D = 8 in.

E = 10 in.

F = 12 in.

G = 15 in.

H = 18 in.

J = 21 in.

K = 24 in.

Illustration shows adjustment 3.

11 Spring Guards

6 in. spring guards at each end are standard.

X = No spring guards

This option should only be used in static bend applications.